PRODUCT CATALOG 2021 KEOFITT SINGLE-PORT









KEOFITT SINGLE-PORT

Replace your ordinary, non-hygienic sampling cocks with the KEOFITT Single-Port Sampling Valve.


This valve is CIP-able with process CIP and still true to the Keofitt concept, as it is available with various process connections with manual or pneumatic operation.






- 54 -

HOW IT WORKS





- 56 -

KEOFITT SINGLE-PORT W9™ SAMPLING VALVE

The KEOFITT Single-Port W9[™] sampling valve is our solution for CIP-able sampling from less demanding applications. If the BASIX[™] does not cover your need due its smaller size, the 9mm outlet on the Single-Port W9 will do the job. With the W9-solution you have the added benefit of choosing products from a selected range within the W9 product outline.

This valve is designed for sampling of products with a viscosity of 0-1000 cP with particles up to 3 mm in diameter.

The Single-Port W9 valve is usable for simple, hygienic sampling in all industries for products such as:

Water

Milk

Perfume


Fruit juice

Available in many versions; choose your preferred type of head from our W9 product outline.




-57-

KEOFITT SINGLE-PORT W9 - BODIES




- 58 -






^{*} CHOOSE VALVE HEAD AND PARTS & ACCESSORIES FROM THE W9 SECTION

HOW IT WORKS





- 60 -

KEOFITT BASIX SAMPLING VALVE

The KEOFITT BASIX™ Sampling Valve is our basic CIP-able sampling valve for less demanding applications. The KEOFITT BASIX™ Sampling Valve is our product category for process CIP-able sampling valves for less demanding applications that require no separate inlet for sterilizing or sanitizing media.

This valve is designed for sampling of low viscosity products in the range of 0-100 cP with particles less than 1,5 mm in diameter.

Basix[™] is used for simple, hygienic sampling in all industries for products such as:

Water

Milk

Perfume

Fruit Juice

Available in manual and pneumatic versions this valve is offered complete as a valve body and valve head combination.

Choose from silicone, EPDM or PTFE membranes.



-61-

KEOFITT BASIX SAMPLING VALVES

	MANUAL VALVE						
			TANK WELDING	PIPE WELDING	MINI CLAMP	1" & 1½" CLAMP	
KEOFITT BASIX™	HOSE PIECE						
KEC	HOSE	SILICONE	450141	451141	452141	452241	
		ЕРDМ	450141EPDM	451141EPDM	452141EPDM	452241EPDM	
		PTFE	450141PTFE	451141PTFE	452141PTFE	452241PTFE	

PNEUMATIC VALVE						
TANK WELDING	PIPE WELDING	MINI CLAMP	1" & 1½" CLAMP			
450144	451144	452144	452244			
450144EPDM	451144EPDM	452144EPDM	452244EPDM			
450144PTFE	451144PTFE	452144PTFE	452244PTFE			

-62-

KEOFITT BASIX - PARTS & ACCESSORIES

ES	O-RING	600825 SILICONE 7.1X1.6	550184 FESTO	800830 SILICONE 10.3X2.4	830830E EPDM 10.3X2.4
	MEMBRANE	400051 SILICONE	400052 EPDM	400055 PTFE	
k ACCESSORI	FOR HOSE PIECE	550002 PTFE QC 0.5M	550003 PTFE QC 1.0M	550002.2 PTFE QC/TC O.5M	550003.2 PTFE QC/TC 1M
BASIXT" PARTS & ACCESSORIES		800083 QC TC	900045 QC SYRINGE INJECTION	600062 RUBBER CAP	450063 SINGLE ST.ST. CHAIN
	MISC.	600170 LEVER HANDLE Q/N	600370 LEVER HANDLE SELF-CLOSING	800052 HOSE PIECE/HOSE PIECE W9	400255 TOOL FOR MEMBRANE (PTFE)
		900091 GASKET EPDM 1"	900018 TOMMY BAR	900031 HP W9/MALE THREAD M12	900047 TUBE PTFE 10/8MM

- 64 -

