

Alfa Laval LKH Evap

Centrifugal pumps

Introduction

The Alfa Laval LKH Evap Centrifugal Pump is a premium pump for use in hygienic applications. As a low-NPSHr, high-efficiency centrifugal pump, the LKH Evap is a tailored evaporator pump supported by strong and extensive documentation, including a comprehensive vacuum curve package. It features a special scraper impeller, ClearFlow, that solves the product buildup problem in high solids applications, which can prolong production time between cleaning.

Precision-engineered, the LKH Evap pump delivers greater energy efficiency than similar pumps. Its optimized design, premium motor, tight tolerances and advanced impeller design minimize recirculation and reduce energy consumption.

Applications

The LKH Evap Centrifugal Pump is designed for hygienic applications across the dairy, food, beverage, brewery, alcohol, ethanol, starch and chemical industries. It is ideal for use in evaporation duties for applications, such as liquid concentration and powder processing as well as plant and equipment dewatering.

The LKH Evap pump is available in 10 sizes to handle capacities up to 280 m3/h and differential pressures up to 11 bar at 50 Hz.

Benefits

- Energy efficient: superior efficiency resulting in reduced energy consumption and CO2 footprint.
- Hygienic: designed according to the most stringent hygienic design standards and with verified and effective Cleaning-in-Place.
- Low NPSHr: reduced NPSHr enables optimized system designs.
- Maximized uptime and reduced maintenance costs: robust mechanical design and ease of maintenance with modular front-loading seals.

Standard design

All media contacting steel components like pump casing, impeller, impeller nut and backplate are in W. 1.4404 (AISI 316L). A stainless steel shroud protects the motor and four adjustable stainless steel legs support the complete unit.

A compression coupling securely attaches the stub shaft to the motor shaft with precision alignment, and the semi-open impeller with a special vane design ensures efficient and gentle handling of the product as it moves through the pump.

As standard, the LKH Evap pump is equipped with a single mechanical shaft seal but is also available with a single flushed or a double mechanical shaft seal. The front-loading shaft seal, with the spring and washers mounted on the atmospheric side, makes maintenance fast, easy and inexpensive. It takes just a few minutes to replace the shaft seal. In addition, the balanced design minimizes the risk of seal opening during unforeseen pressure shock.

LKH Evap is available with the Clear Flow Impeller which is to be used in applications where there is a risk of building up a hard layer of product between impeller and backplate.






TECHNICAL DATA

Product wetted steel parts:	W. 1.4404 (316)
Other steel parts:	Stainless ste
nside surface finish:	Standard blaste
Product wetted elastomers:	EPD
Ratary seal face:	Carbo
Stationary seal face:	Silicon Carbio
Motor Control of the	
Foot-flanged motor according to the IEC metric standard, 2 poles = 3000/3600 rpm a	t 50/60 Hz, 4 poles = 1500/1800 rpm at 50/60 Hz, IP 55
with drain hole with labyrinth plug), insulation class F.	
Motor sizes	
50Hz:	1.5 - 75 k
50Hz:	1.2 - 80 k
Min/max motor speed	
2 poles: 1.5 - 45 kW:	900 - 4000 rp
2 poles: 55 - 75 kW:	900 - 3600 rp
poles: 1.5 - 75 kW:	900 - 2200 rp
•	ts on the condition that genuine Alfa Laval Spare Parts are use
Extended 3-years warranty on LKH Evap pumps. The warranty covers all non wear part	ts on the condition that genuine Alfa Laval Spare Parts are use
Warranty Extended 3-years warranty on LKH Evap pumps. The warranty covers all non wear part PPERATING DATA Max inlet pressure	
Extended 3-years warranty on LKH Evap pumps. The warranty covers all non wear part PERATING DATA Max inlet pressure LKH Evap 10 - 70:	ts on the condition that genuine Alfa Laval Spare Parts are use
Extended 3-years warranty on LKH Evap pumps. The warranty covers all non wear part PERATING DATA Max inlet pressure LKH Evap 10 - 70:	1000kPa (10 b
Extended 3-years warranty on LKH Evap pumps. The warranty covers all non wear part PPERATING DATA Max inlet pressure LKH Evap 10 - 70: LKH Evap 70, 60Hz:	1000kPa (10 b. 500kPa (5 b.
Extended 3-years warranty on LKH Evap pumps. The warranty covers all non wear part PERATING DATA Max inlet pressure LKH Evap 10 - 70: LKH Evap 70, 60Hz: Temperature	1000kPa (10 b
Extended 3-years warranty on LKH Evap pumps. The warranty covers all non wear part PPERATING DATA Max inlet pressure LKH Evap 10 - 70: LKH Evap 70, 60Hz: Temperature Temperature range:	1000kPa (10 b 500kPa (5 b -10°C to +140°C (EPD
Extended 3-years warranty on LKH Evap pumps. The warranty covers all non wear part PPERATING DATA Max inlet pressure LKH Evap 10 - 70: LKH Evap 70, 60Hz: Femperature Femperature range: Flush media:	1000kPa (10 b 500kPa (5 b -10°C to +140°C (EPD
Extended 3-years warranty on LKH Evap pumps. The warranty covers all non wear part PPERATING DATA Max inlet pressure LKH Evap 10 - 70: LKH Evap 70, 60Hz: Femperature Emperature range: Flush media:	1000kPa (10 b. 500kPa (5 b.
Extended 3-years warranty on LKH Evap pumps. The warranty covers all non wear part PPERATING DATA Max inlet pressure LKH Evap 10 - 70: LKH Evap 70, 60Hz: Pemperature Emperature range: Flush media: Flushed shaft seal Vater pressure inlet:	1000kPa (10 b 500kPa (5 b -10°C to +140°C (EPD Max 70 Max. 1 b
Extended 3-years warranty on LKH Evap pumps. The warranty covers all non wear part PERATING DATA Max inlet pressure KH Evap 10 - 70: KH Evap 70, 60Hz: Temperature Temperature range: Telush media: Tushed shaft seal Vater pressure inlet: Vater consumption:	1000kPa (10 b 500kPa (5 b -10°C to +140°C (EPD Max 70 Max. 1 b
Extended 3-years warranty on LKH Evap pumps. The warranty covers all non wear part PPERATING DATA Max inlet pressure LKH Evap 10 - 70: LKH Evap 70, 60Hz: Temperature Temperature range: Flush media: Flushed shaft seal Water pressure inlet: Water consumption:	1000kPa (10 b 500kPa (5 b -10°C to +140°C (EPD Max 70
Extended 3-years warranty on LKH Evap pumps. The warranty covers all non wear part PERATING DATA Max inlet pressure KH Evap 10 - 70: KH Evap 70, 60Hz: Femperature Femperature range: Filush media: Filushed shaft seal Vater pressure inlet: Vater consumption: Double mechanical shaft seal Vater pressure inlet, LKH Evap 10 to 60:	1000kPa (10 b 500kPa (5 b -10°C to +140°C (EPD Max 70 Max. 1 b 0.25 - 0.5 l/n
Extended 3-years warranty on LKH Evap pumps. The warranty covers all non wear part PPERATING DATA Max inlet pressure LKH Evap 10 - 70: LKH Evap 70, 60Hz: Femperature Femperature range: Flush media: Flushed shaft seal Nater pressure inlet: Nater consumption: Double mechanical shaft seal Nater pressure inlet, LKH Evap 10 to 60: Nater pressure inlet, LKH Evap 70:	1000kPa (10 b 500kPa (5 b -10°C to +140°C (EPD Max 70 Max. 1 b 0.25 - 0.5 l/n
Extended 3-years warranty on LKH Evap pumps. The warranty covers all non wear part	1000kPa (10 b 500kPa (5 b -10°C to +140°C (EPE Max 70 Max. 1 l 0.25 - 0.5 l/r Max. 500 kPa (5 b Max. 300 kPa (3 b

Dimensions (mm)



Pump specific measures

Pump Model	LKHevap-10	LKHevap-15	LKHevap-20	LKHevap-25	LKHevap-35	LKHevap-40	LKHevap-45	LKHevap-50	LKHevap-60	LKHevap-70
Α	142	166	180	193	193	212	212	205	261	254
В	87	66	88	106	119	126	126	118	102	147
C	23	43	27	32	23	28	28	35	62	25
D	247	247	253	303	303	329	329	329	329	408
<u>E</u>	51	87	63	69	54	64	64	77	106	76

Motor specific measures

meter epecine medearee								
Motor IEC	IEC90	IEC100	IEC112	IEC132	IEC160	IEC180	IEC200	IEC250
Motor kW	1.5/2.2	3.0	4.0	5.5/7.5	11/15/18.5	22	30/37/45	55/75
F(max)*	262	282	285	304	332	352	372	446
G	157	185	198	196	262	286	399	394
<u>H</u>	288	325	359	383	485	533	670	738
I (LKHevap-10 to -60)	434	516	497	597	791	842	980	-
I (LKHevap-70)	-	_	-	-	804	855	993	1051

^{*}Possible to reduce dimension F by min. 59 mm for all pump models. For smaller models it will be possible to reduce dimension F even further.

Motor overview


Pump Model	LKHevap-10	LKHevap-15	LKHevap-20	LKHevap-25	LKHevap-35	LKHevap-40	LKHevap-45	LKHevap-50	LKHevap-60	LKHevap-70
Moter range (IEC)	IEC90-	IEC100-	IEC90-	IEC132-	IEC112-	IEC132-	IEC112-	IEC132-	IEC132-	IEC132-
	IEC112	IEC132	IEC132	IEC160	IEC160	IEC180	IEC160	IEC180	IEC200	IEC250

Dimensional data are based on 2 pole, ABB motors.

Connections								
Pump Model		LKHevap-10 LKHevap-20 LKHevap-35	LKHevap-15 LKHevap-45 LKHevap-50 LKHevap-70	LKHevap-15 LKHevap-45 LKHevap-50	LKHevap-25	LKHevap-40	LKHevap-60	LKHevap-60
Clamp ISO 2037	M1	21	21	102	21	21	21	102
	M2	21	21	21	21	12	21	21
Union ISO(IDF)	M1	21	21	102	21	21	21	102
	M2	21	21	21	21	21	21	21
Union DIN/ISO	M1	25	30	111	30	30	30	111
	M2	22	30	30	25	27	30	30
Union SMS	M1	24	35	105	24	24	35	105
	M2	20	24	24	24	24	35	35
Union (BS)RJT	M1	27	32	108	27	27	32	108
	M2	27	27	27	27	22	32	32
Union DS	M1	24	24	105	24	24	24	105
	M2	20	24	24	24	21	24	24
Union DIN/DIN	M1	25	30	111	30	30	30	111
	M2	22	30	30	25	27	30	30
J1*		63,5 / 2,5"	101,6 / 4"	76,1 / 3"	76,1 / 3"	76,1 / 3"	101,6 / 4"	76,1 / 3"
J2*		51 / 2"	76,1 / 3"	76,1 / 3"	63,5 / 2,5"	63,5 / 2,5"	101,6 / 4"	101,6 / 4"

 $^{^{\}star}$ Other dimensions available on request. $\ensuremath{\mathsf{ESE}01863/8}$

Flow chart



Note: If Clear Flow impeller is mounted the performance can be up to 10% lower than shown on the curves above

Options

- A. Impeller with reduced diameter.
- B. Flushed shaft seal.
- C. Double mechanical shaft seal.
- D. Rotating seal face of Silicon Carbide.
- E. Product wetted elastomers NBR, FPM or FEP.
- F. 1/2" vertical drain connection.
- G. Product wetted surface finish mechanically polished to Ra \leq 0.8 μ m.
- H. Surface finish measurement with certificate (Ra \leq 0.8 μ m).
- I. Inducer (LKH Evap 10 to 50).
- J. Adjustable pads.
- K. Motor for other voltage and/or frequency.
- L. Half speed motor.
- M. Motor with increased safety/flame proof motor.

Ordering

Please state the following when ordering:

- Pump size.
- Connections.
- Impeller diameter.
- Motor size.
- Voltage and frequency.
- Flow, pressure and temperature.
- Density and viscosity of the product.
- Options.

Note!

For further details, see also instruction manual.

Alfa Laval reserves the right to change specifications without prior notification.

How to contact Alfa Laval

Contact details for all countries are continually updated on our website. Please visit www.alfalaval.com to access the information direct.