


# DELTA CPV

CONSTANT PRESSURE VALVE

The DELTA CPV constant pressure membrane valve is designed to ensure constant product pressures in the hygienic process technology and aseptic plants. It is suitable for use in the dairy, food, brewing, and beverage as well as personal care and pharmaceutical industries.

## Method of operation

The effective principle of the pressure maintaining is based on the diminution and enlargement of the free flow section at the valve seat by the valve cone. This cone is connected to the regulating membrane via the valve shaft. The regulating membrane is backed up with air at a set pressure. Thus, if any product pressure changes occur, the valve membrane immediately reacts and changes the position of the cone, ensuring that the pre-set product pressure is maintained.



## Application range

The DELTA CPV is available for two generic functions:

- DELTA CPV-o: to keep pressure constant upstream of the valve
- DELTA CPV-c: to keep pressure constant downstream of the valve

The DELTA CPV-o is typically used:

- In UHT systems to prevent boiling in heat exchangers
- In pasteurizers to ensure a positive pressure difference between the pasteurised and unpasteurised sections.
- In a re-circulation loop in front upstream of a filling machine to ensure a constant pressure to the filler
- To maintain a constant pressure in a separator.

The DELTA CPV-c is typically used:

- Upstream of a packaging machine
- In a water supply system

## Features and benefits

### Maximum product protection / product care

- The round surfaces in the housing and on the modulating cone ensure minimum shear forces applied onto the product
- Stable and excellent modulating quality - precise control of the valve cone by the multi-layer flat membrane system
- Minimised product volume in the valve housing ensures a quick response time and excellent modulating accuracy .  
The housing can be welded in-line - no additional seals required

### Extended operating time

- The rubber-supported TFM membrane system is provided a long operating lifetime.
- Excellent cleanability  
Flat TFM membrane - smooth housing surface - no dead areas and no crevices
- The large kv value within the fully open valve provides for sufficient CIP throughput during pipe cleaning - no additional by-pass required

## Ease of use

- Flat membrane system with integrated leak detection for quick indication of any leakage from the product side or air side
- The large kv value combined with the modulating quality ensures a broad field of applications
- Optional booster available to support insufficient air supply pressure.

<b>SIZES</b>	2" - ISO 2037, DN50 - DIN 11850	
<b>WORKING PRODUCT PRESSURE</b>	Up to 7 bar	
<b>MAX. OPERATING PRODUCT PRESSURE</b>	10 bar	
<b>MAX. SUPPLY AIR PRESSURE (INCL. BOOSTER)</b>	4 bar	
<b>TEMPERATURE</b>	Max. operating	135 °C
	Short term	140 °C
<b>AIR CONNECTION</b>	G 1/8"	
<b>HOUSING MATERIAL</b>	1.4404	
<b>MEMBRANE MATERIAL</b>	Product wetted side:	TFM
	Rear side:	EPDM covered



SPX Flow Technology, Zechenstrasse 49, D-59425 Unna, Germany

Phone: +49 (0) 23 03/ 108-0 Fax: +49 (0) 23 03 / 108-210

SPX reserves the right to incorporate our latest design and material changes without notice or obligation.

Design features, materials of construction and dimensional data, as described in this bulletin, are provided for your information only and should not be relied upon unless confirmed in writing. Please contact your local sales representative for product availability in your region. For more information visit [www.spx.com](http://www.spx.com).

The green ">" is a trademark of SPX Corporation, Inc..

APV-8012-GB Version: 03/2014 Issued: 02/2014

[www.sks-online.com](http://www.sks-online.com)

COPYRIGHT © 2008, 2014 SPX Corporation